



# Power Protection Products, GFCI Plug-In, Commercial, Auto Set, 15A 120 V AC, 3) 5-15R, 5 Protected Outlets, 4-6 mA Trip Level, Yellow

By Bryant  
Catalog # [GFP153R](#)



Power Protection Products, GFCI Plug-In, Commercial, Auto Set, 15A 120 V AC, 3) 5-15R, 5 Protected Outlets, 4-6 mA Trip Level, Yellow.

## General

Catalog Number	GFP153R
Color	
Construction	Fabricated
EU RoHS Indicator	No
Item Type	Industrial/Commercial Grade
Material - Insulation	Elastomer
Material - Jacket	PVC
Series	Commercial
Style	Manual Set
Temperature Rating	-35 Degrees C to 66 Degrees C (-30 Degrees F to 150 Degrees F)
Type	Plug-In
UPC	781786704503

## Dimensions

Outside Diameter	0.35
Weight	0.75 lb

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Plug-In
Current / Amperage Rating	15 A
Current Rating	15 A
Voltage Rating	120 VAC
Voltage Rating Description	120 VAC

## Conductor Related

Conductor Size	#14 AWG
Conductor Type	Copper
Number of Conductors	3
Strands	Multi

## Logistics

Carton Quantity	50
-----------------	----

## Product Assets



A Hubbell brand