



Circuit Watch Surge Suppression Straight Blade Receptacle, Industrial/Commercial Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5- 15R, Brown

By Bryant
Catalog # SP52A



Circuit Watch Surge Suppression Straight Blade Receptacle,
Industrial/Commercial Grade, 15A 125V, 2-Pole 3-Wire
Grounding, 5-15R, Brown.

General

Application	Duplex with Light and Alarm
Catalog Number	SP52A
Color	
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	LED and Audible Alarm
Item Type	Surge Protection Receptacles
Material	Composite
Material - Mounting Hardware	Mounting Screws
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade
Response Time	5
Series	Specification Grade
Style	Surge Protection Only
Type	Duplex Receptacle
UPC	781786139008

Dimensions

Display Size	Standard
--------------	----------

Electrical Ratings

Amperage Rating	15 A
Connectivity	Terminal Screws
Current / Amperage Rating	15 A
Current Rating	15 A
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

Certifications And Compliance

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY_CA-SP52A-SPEC-EN | REV 6/2024