



# Industrial Grade, Toggle Switches, Motor Disconnects, Three Pole, 30A 600V AC, Side Wired Only, Aluminum, With NEMA 1 Enclosure

By Bryant  
Catalog # 30103D



Switches and Lighting Controls, Industrial Grade, Toggle  
Switches, Motor Disconnects, Three Pole, 30A 600V AC, Side  
Wired Only, Aluminum, With NEMA 1 Enclosure

## Application

Standard Toggle

## General

Catalog Number	30103D
EU RoHS Indicator	No
Enclosure Type	NEMA 1
Environmental Conditions	Indoor Only
Item Type	Enclosed Switch
Load Capacity	Inductive
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3 Pole
Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Minimum Continuous -40 Deg C without Impact
Series	Non-Fused
Style	Standard Duty
Type	Disconnect Switches
UPC	781786631564

## Dimensions

Display Size Standard Sized Product

## Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Phase	Three Phase
Voltage Rating	600V AC kV
Voltage Rating Description	600V AC kV
Wattage	18000

## Certifications And Compliance

Standards - RoHS Compliance CM  
Status

## Logistics

Carton Quantity 10

## Product Assets

[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - 30103D](#)