



# Switches and Lighting Controls, Industrial Grade, Toggle Switches, Motor Disconnects, Three Pole, 30A 600V AC, Side Wired Only, With NEMA 3R Enclosure

By Bryant  
Catalog # 30303D



Switches and Lighting Controls, Industrial Grade, Toggle  
Switches, Motor Disconnects, Three Pole, 30A 600V AC, Side  
Wired Only, Black, With NEMA 3R Enclosure

## Application

Red Slide

## General

Catalog Number	30303D
EU RoHS Indicator	No
Enclosure Type	NEMA 3R
Environmental Conditions	Indoor and Outdoor
Item Type	Enclosed Switch
Load Capacity	Inductive
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3 Pole
Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Minimum Continuous -40 Deg C without Impact
Series	Non-Fused
Style	Standard Duty
Type	Disconnect Switches
UPC	781786631588

## Dimensions

Display Size

Standard Sized Product

## Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Phase	Three Phase
Voltage Rating	600V AC kV
Voltage Rating Description	600V AC kV
Wattage	18000

## Logistics

Carton Quantity	4
Pallet Quantity	480

## Product Assets

[Catalogs - Bryant Full Line Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Specifications - 30303D](#)