



# Locking Devices, Locking Devices, Industrial, Flush Receptacle, 30A 250V, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Black

By Bryant  
Catalog # 3330



Locking Devices, Locking Devices, Industrial, Flush Receptacle,  
30A 250V, 2-Pole 3-Wire Grounding, Non-NEMA, Screw  
Terminal, Black

## Application

Extra Heavy Duty Industrial Specification Grade

## General

Catalog Number	3330
EU RoHS Indicator	No
Environmental Conditions	Indoor Only
Item Type	30A Single Nylon Receptacle
Material	Nylon
Material - Mounting Hardware	Plug-In
Number Of Poles	3-Pole
Style	Single Receptacle
Type	Receptacle
UPC	781786619685

## Dimensions

Dimensions	3.28 in x 1.71 in x 1.20 in
Display Size	Standard Sized Product
Height	1.2 in
Length	3.28 in
Width	1.71 in

## Electrical Ratings

Amperage Rating	30 A
Connectivity	Terminal Screws
Current Rating	30 A
Phase	Multi Phase
Voltage Rating	125/250 VAC
Voltage Rating Description	125/250V AC

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG

## Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - 3330](#)