



# Locking Devices, Locking Devices, Industrial, Flush Receptacle, 30A 3-Phase Wye 120/208V AC, 4-Pole 4-Wire Non- Grounding, Non-NEMA, Screw Terminal

By Bryant  
Catalog # 3430BRY



Locking Devices, Industrial, Flush Receptacle, 30A 3-Phase Wye 120/208V AC, 4-Pole 4-Wire Non-Grounding, Non-NEMA, Screw Terminal, Black.

## Features

- Flush Receptacle
- 30A 3-Phase Wye 120/208V AC
- 4-Pole 4-Wire Non-Grounding
- Non-NEMA
- Screw Terminal

## Application

Extra Heavy Duty Industrial Specification Grade

## General

Catalog Number	3430BRY
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	30A Single Nylon Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	4-Pole
Style	Single Receptacle
Type	Receptacle
UPC	781786619906

## Dimensions

Dimensions	3.28 in x 1.70 in x 1.24 in
Display Size	Standard Sized Product

Height	1.24 in
Length	3.28 in
Width	1.7 in

## Electrical Ratings

Amperage Rating	30 A
Connectivity	Terminal Screws
Current Rating	30 A
Phase	Three Phase
Voltage Rating	3 Phase Y 120/208 VAC
Voltage Rating Description	3 Phase Y 120/208V AC

## Conductor Related

Number Of Wires	4-Wire
Wire Size	#14 AWG to #8 AWG

## Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - 3430BRY](#)