



Locking Devices, Locking Devices, Industrial, Female Connector Body, 30A 3-Phase Wye 120/208V AC, 4-Pole 4-Wire Non- Grounding, Non-NEMA

By Bryant
Catalog # 3433



Locking Devices, Locking Devices, Industrial, Female Connector Body, 30A 3-Phase Wye 120/208V AC, 4-Pole 4-Wire Non-Grounding, Non-NEMA, Screw Terminal, Black and White

Application

Heavy Duty Industrial

General

Catalog Number	3433
Color	Black
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	30A Triple Gripper Nylon Connector Non-NEMA
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	4-Pole
Style	Internal Cord Clamp
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body
UPC	781786619944

Dimensions

Dimensions	2.13 in x 2.13 in x 3.90 in
Display Size	Standard Sized Product
Height	3.9 in

Length	2.13 in
Width	2.13 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Screw Terminals
Current Rating	30 A
Voltage Rating	3 Phase Y 120/208 VAC
Voltage Rating Description	3 Phase Y 120/208 VAC

Conductor Related

Conductor Range	#12 AWG to #8 AWG
Number Of Wires	4-Wire
Number of Conductors	4-Wire Non-Grounding
Wire Size	#18 AWG to #8 AWG

Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - Bryant Full Line Catalog Specifications - 3433](#)