



# Locking Devices, Locking Devices, Industrial, Flush Receptacle, 50A 250V DC/600V AC, 3-Pole 4-Wire Grounding, Non- NEMA, Screw Terminal, Black

By Bryant  
Catalog # 3769



Locking Devices, Industrial, Flush Receptacle, 50A 250V  
DC/600V AC, 3-Pole 4-Wire Grounding, Non- NEMA, Screw  
Terminal, Black

## Features

- Flush Receptacle
- 50A 250V DC/600V AC
- 3-Pole 4-Wire Grounding
- Non- NEMA
- Screw Terminal

## Application

Extra Heavy Duty Industrial Specification Grade

## General

Catalog Number	3769
Color	Black
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	50A Single Armored Heavy Duty Receptacle-For Replacement Use
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Style	Extra Heavy Duty
Type	Receptacle
UPC	781786652804

## Dimensions

Dimensions	3.28 in x 2.12 in x 2.44 in
Display Size	Standard Sized Product
Height	2.44 in
Length	3.28 in
Width	2.12 in

## Electrical Ratings

Amperage Rating	50 A
Connectivity	Pressure Terminal Screws
Current Rating	50 A
Phase	Multi Phase
Voltage Rating	250 VDC/600 VAC
Voltage Rating Description	250 VDC/600 VAC

## Conductor Related

Number Of Wires	4-Wire
Wire Size	#14 AWG to #10 AWG

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - 3769](#)