



## Switches and Lighting Controls, Industrial Grade, Toggle Switches, Motor Disconnects, Double Pole, 40A, 600V AC, Side Wired Only, Black

By Bryant  
Catalog # 40002D



Switches and Lighting Controls, Industrial Grade, Toggle  
Switches, Motor Disconnects, Double Pole, 40A, 600V AC, Side  
Wired Only, Black

### General

Catalog Number	40002D
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Open Switch
Load Capacity	Inductive
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2 Pole
Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Minimum Continuous -40 Deg C without Impact
Series	Standard Toggle
Style	Motor Controller/Disconnect
Type	Side Wire
UPC	781786631632

### Dimensions

Display Size	Standard Sized Product
--------------	------------------------

### Electrical Ratings

Amperage Rating	40 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	40 A
Current Rating	40 A
Phase	Single Phase
Voltage Rating	600V AC kV
Voltage Rating Description	600V AC kV
Wattage	24000

### Certifications And Compliance

Standards - RoHS Compliance Status	CM
---------------------------------------	----

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - 40002D](#)