



Locking Devices, Locking Devices, Isolated Ground Industrial, Flush Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, L5-15R, Screw Terminal, Orange

By Bryant
Catalog # 4710IG



Locking Devices, Isolated Ground Industrial, Flush Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, L5-15R, Screw Terminal, Orange

General

Application	Extra Heavy Duty Industrial Specification Grade
Catalog Number	4710IG
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	15A Nylon Single Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Series	Locking
Style	Isolated Ground
Type	Single Receptacle
UPC	781786656147

Dimensions

Dimensions	3.28 in x 1.41 in x 1.01 in
Display Size	Standard Sized Product
Height	1.01 in
Length	3.28 in
Width	1.41 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Terminal Screws
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG

Certifications And Compliance

Nema Rating	L5-15R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
Pallet Quantity	4800

Product Assets

[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY_MX-4710IG-SPEC-EN | REV 6/2024