



# Straight Blade Devices, Receptacles, Single, Commercial/Industrial Grade, Isolated Ground, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Gray, Single Pack



By Bryant  
Catalog # 5261IGGRY

Straight Blade Devices, Receptacles, Single,  
Commercial/Industrial Grade, Isolated Ground, 2-Pole 3-Wire  
Grounding, 15A 125V, 5-15R, Gray, Single Pack

## Features

- Single
- Commercial/Industrial Grade
- Isolated Ground
- 2-Pole 3-Wire Grounding
- 15A 125V

## Application

Extra Heavy Duty Industrial Specification Grade

## General

Catalog Number	5261IGGRY
Color	Gray
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Single
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Series	Straight Blade
Style	Finder Groove Face
Type	Single Receptacle
UPC	781786714021

## Dimensions

Dimensions	3.28 in x 1.38 in x 0.91 in
Display Size	Standard Sized Product

Height	0.91 in
Length	3.28 in
Weight	0.1 lb
Width	1.38 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

## Certifications And Compliance

Nema Rating	5-15R
-------------	-------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - 5261IGGRY](#)