



Switches and Lighting Controls, Industrial Grade, Toggle Switches, Manual Motor Controllers, Double Pole, 60A 600V AC, Side Wired Only, Black

By Bryant
Catalog # 60002D



Switches and Lighting Controls, Industrial Grade, Toggle Switches, Manual Motor Controllers, Double Pole, 60A 600V AC, Side Wired Only, Black

Features

- Toggle
- Manual Motor Controllers
- Double Pole
- 60A 600V AC
- Side Wired Only

General

Catalog Number	60002D
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Open Switch
Load Capacity	Inductive
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2 Pole
Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Minimum Continuous -40 Deg C without Impact
Series	Standard Toggle
Style	Motor Controller/Disconnect
Type	Back Wire
UPC	781786631694

Dimensions

Display Size Standard Sized Product

Electrical Ratings

Amperage Rating	60 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	60 A
Current Rating	60 A
Phase	Single Phase
Voltage Rating	600V AC kV
Voltage Rating Description	600V AC kV
Wattage	36000

Certifications And Compliance

Standards - RoHS Compliance CM Status

Logistics

Carton Quantity 10

Product Assets

[Catalogs - Bryant Full Line Catalog](#)
[Specifications - 60002D](#)