



Switches and Lighting Controls, Industrial Grade, Toggle Switches, Manual Motor Controllers, Three Pole, 60A 600V AC, Side Wired Only, Black

By Bryant
Catalog # 60003D



Switches and Lighting Controls, Industrial Grade, Toggle
Switches, Manual Motor Controllers, Three Pole, 60A 600V AC,
Side Wired Only, Black

General

Catalog Number	60003D
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Open Switch
Load Capacity	Inductive
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3 Pole
Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Minimum Continuous -40 Deg C without Impact
Series	Standard Toggle
Style	Motor Controller/Disconnect
Type	Back Wire
UPC	781786631748

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	60 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	60 A
Current Rating	60 A
Phase	Three Phase
Voltage Rating	600V AC kV
Voltage Rating Description	600V AC kV
Wattage	36000

Certifications And Compliance

Standards - RoHS Compliance Status	CM
---------------------------------------	----

Logistics

Carton Quantity	10
Pallet Quantity	1170

Product Assets

[Catalogs - Bryant Full Line Catalog](#)
[Specifications - 60003D](#)