



Industrial Grade, Toggle Switches, Manual Motor Controllers, Three Pole, 60A 600V AC, Side Wired Only, With NEMA 3R Enclosure

By Bryant
Catalog # 60303D



Switches and Lighting Controls, Industrial Grade, Toggle
Switches, Manual Motor Controllers, Three Pole, 60A 600V AC,
Side Wired Only, Black, With NEMA 3R Enclosure

Application

Red Slide

General

| | |
|------------------------------|--|
| Catalog Number | 60303D |
| EU RoHS Indicator | No |
| Enclosure Type | NEMA 3R |
| Environmental Conditions | Indoor and Outdoor |
| Item Type | Enclosed Switch |
| Load Capacity | Inductive |
| Material - Mounting Hardware | Screw Mounting |
| Number Of Poles | 3 Pole |
| Operating Cycles | 10,000 Cycles Minimum |
| Operating Temperature | Minimum Continuous -40 Deg C without Impact |
| Series | Non-Fused |
| Style | Standard Duty |
| Type | Disconnect Switches |
| UPC | 781786631786 |

Dimensions

Display Size Standard Sized Product

Electrical Ratings

| | |
|----------------------------|--------------------------|
| Amperage Rating | 60 A |
| Connectivity | Pressure Terminal Screws |
| Current / Amperage Rating | 60 A |
| Current Rating | 60 A |
| Phase | Three Phase |
| Voltage Rating | 600V AC kV |
| Voltage Rating Description | 600V AC kV |
| Wattage | 36000 |

Certifications And Compliance

Standards - RoHS Compliance CM
Status

Logistics

Carton Quantity 4

Product Assets

[Catalogs - Bryant Full Line Catalog](#)
[Specifications - 60303D](#)