



Locking Devices, Isolated Ground, Industrial, Flush Receptacle, 30A 125V, 2-Pole 3-Wire Grounding, L5- 30R, Screw Terminal, Black

By Bryant
Catalog # 70530IG



Application

Extra Heavy Duty Industrial Specification Grade

General

Catalog Number	70530IG
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	30A Single Nylon Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Series	Locking
Style	Isolated Ground
Type	Single Receptacle
UPC	781786688759

Dimensions

Dimensions	3.28 in x 1.70 in x 1.24 in
Display Size	Standard Sized Product
Height	1.24 in
Length	3.28 in
Width	1.7 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Terminal Screws
Current Rating	30 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG

Certifications And Compliance

Nema Rating	L5-30R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - Bryant Full Line Catalog](#)
[Specifications - 70530IG](#)