



Locking Devices, Industrial, Flanged Inlet, 30A 125V, 2-Pole 3-Wire Grounding, L5-30P, Screw Terminal, White

By Bryant
Catalog # 70530MB



Locking Devices, Industrial, Flanged Inlet, 30A 125V, 2-Pole 3-Wire Grounding, L5-30P, Screw Terminal, White

Application

Extra Heavy Duty Industrial

General

Catalog Number	70530MB
Color	White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	30A Flanged Inlet
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Style	Equipment Base
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact
Type	Flanged Inlet
UPC	781786688766

Dimensions

Dimensions	2.88 in x 2.88 in x 2.02 in
Display Size	Standard Sized Product
Height	2.02 in

Length	2.88 in
Width	2.88 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Screw Terminals
Current Rating	30 A
Dielectric Strength	Withstands 3500V
Voltage Rating	125 V
Voltage Rating Description	125V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG

Certifications And Compliance

Nema Rating	L5-30P
-------------	--------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - Bryant Full Line Catalog](#)
[Specifications - 70530MB](#)

