



Locking Devices, Industrial, Flush Receptacle, 15A 250V, 2-Pole 3-Wire Grounding, L6-15R, Screw Terminal, Black

By Bryant
Catalog # 70615FR



Locking Devices, Industrial, Flush Receptacle, 15A 250V, 2-Pole 3-Wire Grounding, L6-15R, Screw Terminal, Black

Application

Extra Heavy Duty Industrial Specification Grade

General

Catalog Number	70615FR
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	15A Single Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Style	Single Receptacle
Type	Receptacle
UPC	781786703551

Dimensions

Dimensions	3.28 in x 1.70 in x 1.17 in
Display Size	Standard Sized Product
Height	1.17 in
Length	3.28 in
Width	1.7 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Terminal Screws
Current Rating	15 A
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG

Certifications And Compliance

Nema Rating	L6-15R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
Pallet Quantity	2340

Product Assets

[Catalogs - Bryant Full Line Catalog](#)
[Specifications - 70615FR](#)