




# Locking Devices, Industrial, Flanged Receptacle, 20A 250V, 2-Pole 3-Wire Grounding, L6-20R, Screw Terminal, White

By Bryant  
Catalog # 70620ER



Locking Devices, Industrial, Flanged Receptacle, 20A 250V, 2-Pole 3-Wire Grounding, L6-20R, Screw Terminal, White

## Application

Extra Heavy Duty Industrial Specification Grade

## General

Catalog Number	70620ER
Color	White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	20A Flanged Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Style	Equipment Base
Type	Flanged Receptacle
UPC	781786689206

## Dimensions

Dimensions	2.88 in x 2.88 in x 2.02 in
Display Size	Standard Sized Product
Height	2.02 in
Length	2.88 in
Width	2.88 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Terminal Screws
Current Rating	20 A
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250V

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG

## Certifications And Compliance

Nema Rating	L6-20R
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - 70620ER](#)