



Locking Devices, Industrial, Flanged Receptacle, 20A 277V AC, 2-Pole 3-Wire Grounding, L7-20R, Screw Terminal, White

By Bryant
Catalog # 70720ER



Locking Devices, Industrial, Flanged Receptacle, 20A 277V AC, 2-Pole 3-Wire Grounding, L7-20R, Screw Terminal, White

Application

Extra Heavy Duty Industrial Specification Grade

General

Catalog Number	70720ER
Color	White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	20A Flanged Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Style	Equipment Base
Type	Flanged Receptacle
UPC	781786690004

Dimensions

Dimensions	2.88 in x 2.88 in x 2.02 in
Display Size	Standard Sized Product
Height	2.02 in
Length	2.88 in
Width	2.88 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Terminal Screws
Current Rating	20 A
Phase	Single Phase
Voltage Rating	277 VAC
Voltage Rating Description	277V AC

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG

Certifications And Compliance

Nema Rating	L7-20R
-------------	--------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - Bryant Full Line Catalog](#)
[Specifications - 70720ER](#)