



# Locking Devices, Industrial, Flush Receptacle, 20A 600V AC, 2-Pole 3-Wire Grounding, L9-20R, Screw Terminal, Black

By Bryant  
Catalog # [70920FR](#)



Locking Devices, Industrial, Flush Nylon Receptacle, 20A 600V AC, 2-Pole 3-Wire Grounding, L9-20R, Screw Terminal, Black/White

## Application

Extra Heavy Duty Industrial Specification Grade

## General

Catalog Number	70920FR
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	20A Single Nylon Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Style	Single Receptacle
Type	Receptacle
UPC	781786691636

## Dimensions

Dimensions	3.28 in x 1.70 in x 1.24 in
Display Size	Standard Sized Product
Height	1.24 in
Length	3.28 in
Width	1.7 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Terminal Screws
Current Rating	20 A
Phase	Single Phase
Voltage Rating	600 VAC
Voltage Rating Description	600V AC

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG

## Certifications And Compliance

Nema Rating	L9-20R
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - 70920FR](#)