

# Locking Devices, Industrial, Female Connector Body, 30A 600V AC, 2-Pole 3-Wire Grounding, L9-30R, Screw Terminal, Black and White

By Bryant  
Catalog # [70930NC](#)



Locking Devices, Industrial, Female Connector Body, 30A 600V AC, 2-Pole 3-Wire Grounding, L9-30R, Screw Terminal, Black and White

## Application

Heavy Duty Industrial

## General

Catalog Number	70930NC
Color	Black, White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	30A Triple Gripper Nylon Connector
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Style	Internal Cord Clamp
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body
UPC	781786691995

## Dimensions

Dimensions	2.13 in x 2.13 in x 3.90 in
Display Size	Standard Sized Product
Height	3.9 in
Length	2.13 in

Width 2.13 in

## Electrical Ratings

Amperage Rating	30 A
Connectivity	Screw Terminals
Current Rating	30 A
Voltage Rating	600 VAC
Voltage Rating Description	600 VAC

## Conductor Related

Conductor Range	#12 AWG to #8 AWG
Number Of Wires	3-Wire
Number of Conductors	3-Wire Grounding
Wire Size	#18 AWG to #8 AWG

## Certifications And Compliance

Nema Rating	L9-30R
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity 10

## Product Assets

[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - 70930NC](#)