



Locking Devices, Industrial, Female Connector Body, 20A 250V, 2-Pole 2-Wire Non-Grounding, L2-20R, Screw Terminal, Gray

By Bryant
Catalog # 7101



Locking Devices, Industrial, Female Connector Body, 20A 250V, 2-Pole 2-Wire Non-Grounding, L2-20R, Screw Terminal, Black

Features

- Female Connector Body
- 20A 250V
- 2-Pole 2-Wire Non-Grounding
- L2-20R
- Screw Terminal

Application

Heavy Duty Industrial

General

Catalog Number	7101
Color	Black, White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	20A Connector
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Style	Two-Piece Cord Clamp
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body
UPC	781786627444

Dimensions

Display Size	Standard Sized Product
Height	2.78 in
Length	1.53 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current Rating	20 A
Voltage Rating	250 V
Voltage Rating Description	250 V

Conductor Related

Conductor Range	#14 AWG
Number Of Wires	2-Wire
Number of Conductors	2-Pole Non-Grounding
Wire Size	#18 AWG to #8 AWG

Certifications And Compliance

Nema Rating	L2-20R
-------------	--------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - Bryant Full Line Catalog](#)
[Specifications - 7101](#)