



Locking Devices, Industrial, Female Connector Body, 20A 125/250V, 3-Pole 4-Wire Grounding, L14-20R, Screw Terminal, Black and White

By Bryant
Catalog # 71420NC

Locking Devices, Industrial, Female Nylon Connector Body, 20A 125/250V AC, 3-Pole 4-Wire Grounding, L14-20R, Screw Terminal, Black and White

Application

Heavy Duty Industrial

General

| | |
|------------------------------|---|
| Catalog Number | 71420NC |
| Color | Black, White |
| EU RoHS Indicator | Yes |
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| Insulation | Insulated Body |
| Item Type | 20A Triple Gripper Nylon Connector |
| Material | Composite |
| Material - Mounting Hardware | Cord Mounted |
| Number Of Poles | 3-Pole |
| Style | Internal Cord Clamp |
| Temperature Rating | Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact. |
| Type | Connector Body |
| UPC | 781786695191 |

Dimensions

| | |
|--------------|------------------------|
| Display Size | Standard Sized Product |
| Height | 3.9 in |
| Length | 2.13 in |



Electrical Ratings

| | |
|----------------------------|-----------------|
| Amperage Rating | 20 A |
| Connectivity | Screw Terminals |
| Current Rating | 20 A |
| Voltage Rating | 125/250 VAC |
| Voltage Rating Description | 125/250 VAC |

Conductor Related

| | |
|----------------------|--------------------|
| Conductor Range | #14 AWG to #12 AWG |
| Number Of Wires | 4-Wire |
| Number of Conductors | 4-Wire Grounding |
| Wire Size | #18 AWG to #8 AWG |

Certifications And Compliance

| | |
|------------------------------------|---------|
| Nema Rating | L14-20R |
| Standards - RoHS Compliance Status | CM |

Logistics

| | |
|-----------------|------|
| Carton Quantity | 10 |
| Pallet Quantity | 2160 |

Product Assets

[Catalogs - Bryant Full Line Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Specifications - 71420NC](#)