

Locking Devices, Industrial, Male Plug, 20A 125/250V, 3-Pole 4-Wire Grounding, L14-20P, Screw Terminal, Black and White

By Bryant
Catalog # 71420NP



Locking Devices, Industrial, Male Nylon Plug, 20A 125/250V, 3-Pole 4-Wire Grounding, L14-20P, Screw Terminal, Black and White

Application

- Extra Heavy Duty Industrial

General

Catalog Number	71420NP
Color	Black, White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	20A Triple Gripper Nylon Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
Style	Internal Cord Clamp
Type	Plugs
UPC	781786695221

Dimensions

Dimensions	2.13 in x 2.13 in x 2.86 in
Display Size	Standard Sized
Height	2.86 in
Length	2.13 in
Width	2.13 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125/250 VAC
Voltage Rating Description	125/250 VAC

Conductor Related

Cord Type	All Listed Portables
Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG

Certifications And Compliance

Nema Rating	L14-20P
Standards - RoHS Compliance	CM
Status	

Logistics

Carton Quantity	10
Pallet Quantity	2160

Product Assets

[Catalogs - Bryant Full Line Catalog](#)
[Specifications - 71420NP](#)