



Locking Devices, Isolated Ground, Industrial, Flush Receptacle, 30A 125/250V, 3-Pole 4-Wire Grounding, L14-30R, Screw Terminal, Orange

By Bryant
Catalog # 71430IG



Locking Devices, Isolated Ground, Industrial, Flush Receptacle,
30A 125/250V, 3-Pole 4-Wire Grounding, L14-30R, Screw
Terminal, Orange

Application

Extra Heavy Duty Industrial Specification Grade

General

Catalog Number	71430IG
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	30A Single Nylon Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Series	Locking
Style	Isolated Ground
Type	Single Receptacle
UPC	781786695344

Dimensions

Dimensions	3.28 in x 1.70 in x 1.24 in
Display Size	Standard Sized Product
Height	1.24 in
Length	3.28 in
Width	1.7 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Terminal Screws
Current Rating	30 A
Phase	Single Phase
Voltage Rating	125/250 V
Voltage Rating Description	125/250V AC

Conductor Related

Number Of Wires	4-Wire
Wire Size	#14 AWG to #8 AWG

Certifications And Compliance

Nema Rating	L14-30R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - Bryant Full Line Catalog](#)
[Specifications - 71430IG](#)