



Locking Devices, Industrial, Flush Receptacle, 20A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, L15-20R, Screw Terminal, Black

By Bryant
Catalog # 71520FR



Locking Devices, Industrial, Flush Nylon Receptacle, 20A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, L15-20R, Screw Terminal, Black/White

Application

Extra Heavy Duty Industrial Specification Grade

General

Catalog Number	71520FR
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	20A Single Nylon Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Style	Single Receptacle
Type	Receptacle
UPC	781786695832

Dimensions

Dimensions	3.28 in x 1.70 in x 1.14 in
Display Size	Standard Sized Product
Height	1.14 in
Length	3.28 in
Width	1.7 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Terminal Screws
Current Rating	20 A
Phase	Three Phase
Voltage Rating	3 Phase 250 VAC
Voltage Rating Description	3 Phase 250V AC

Conductor Related

Number Of Wires	4-Wire
Wire Size	#14 AWG to #8 AWG

Certifications And Compliance

Nema Rating	L15-20R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
Pallet Quantity	2080

Product Assets

[Catalogs - Bryant Full Line Catalog](#)
[Specifications - 71520FR](#)