



Locking Devices, Industrial, Flanged Inlet, 30A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, L15-30P, Screw Terminal, White

By Bryant
Catalog # [71530MB](#)



Locking Devices, Industrial, Flanged Inlet, 30A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, L15-30P, Screw Terminal, White

Application

Extra Heavy Duty Industrial

General

| | |
|------------------------------|------------------------------------------------------------------------|
| Catalog Number | 71530MB |
| Color | White |
| EU RoHS Indicator | Yes |
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| Insulation | Insulated Body |
| Item Type | 30A Flanged Inlet |
| Material | Composite |
| Material - Mounting Hardware | Screw Mounting |
| Number Of Poles | 3-Pole |
| Style | Equipment Base |
| Temperature Rating | Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact |
| Type | Flanged Inlet |
| UPC | 781786696167 |

Dimensions

| | |
|--------------|-----------------------------|
| Dimensions | 2.88 in x 2.88 in x 2.02 in |
| Display Size | Standard Sized Product |
| Height | 2.02 in |
| Length | 2.88 in |

Width 2.88 in

Electrical Ratings

| | |
|----------------------------|------------------|
| Amperage Rating | 30 A |
| Connectivity | Screw Terminals |
| Current Rating | 30 A |
| Dielectric Strength | Withstands 3500V |
| Voltage Rating | 3 Phase 250 VAC |
| Voltage Rating Description | 3 Phase 250V AC |

Conductor Related

| | |
|-----------------|-------------------|
| Number Of Wires | 4-Wire |
| Wire Size | #14 AWG to #8 AWG |

Certifications And Compliance

| | |
|------------------------------------|---------|
| Nema Rating | L15-30P |
| Standards - RoHS Compliance Status | CM |

Logistics

Carton Quantity 10

Product Assets

[Catalogs - Bryant Full Line Catalog](#)
[Specifications - 71530MB](#)