



# Locking Devices, Industrial, Flanged Inlet, 30A 3-Phase Wye 120/208V AC, 4-Pole 4-Wire Non-Grounding, L18-30P, Screw Terminal, White

By Bryant  
Catalog # 71830MB



Locking Devices, Industrial, Flanged Inlet, 30A 3-Phase Wye 120/208V AC, 4-Pole 4-Wire Non-Grounding, L18-30P, Screw Terminal, White

## Application

Extra Heavy Duty Industrial

## General

|                              |  |
|------------------------------|--|
| Catalog Number               | 71830MB  |
| Color                        | White  |
| EU RoHS Indicator            | Yes  |
| Environmental Conditions     | Indoor Dry Unless Protected By Additional Means                        |
| Insulation                   | Insulated Body   |
| Item Type                    | 30A Flanged Inlet  |
| Material                     | Composite  |
| Material - Mounting Hardware | Screw Mounting   |
| Number Of Poles              | 4-Pole   |
| Style                        | Equipment Base   |
| Temperature Rating           | Maximum Continuous: 75° C;<br>Minimum Continuous: -40° C<br>w/o impact |
| Type                         | Flanged Inlet  |
| UPC                          | 781786698468   |

## Dimensions

|              |                             |
|--------------|-----------------------------|
| Dimensions   | 2.88 in x 2.88 in x 2.02 in |
| Display Size | Standard Sized Product      |
| Height       | 2.02 in                     |

|        |         |
|--------|---------|
| Length | 2.88 in |
| Width  | 2.88 in |

## Electrical Ratings

|                            |                       |
|----------------------------|-----------------------|
| Amperage Rating            | 30 A                  |
| Connectivity               | Screw Terminals       |
| Current Rating             | 30 A                  |
| Dielectric Strength        | Withstands 3500V      |
| Voltage Rating             | 3 Phase Y 120/208 VAC |
| Voltage Rating Description | 3 Phase Y 120/208V AC |

## Conductor Related

|                 |                   |
|-----------------|-------------------|
| Number Of Wires | 4-Wire            |
| Wire Size       | #14 AWG to #8 AWG |

## Certifications And Compliance

|             |         |
|-------------|---------|
| Nema Rating | L18-20P |
|-------------|---------|

## Logistics

|                 |    |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

## Product Assets

[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - 71830MB](#)