



Locking Devices, Industrial, Male Plug, 20A 3- PhaseWye 277/480V AC, 4-Pole 4-Wire Non-Grounding, L19-20P, Screw Terminal, Black and White

By Bryant
Catalog # 71920NP



Locking Devices, Industrial, Male Nylon Plug, 20A 3-Phase Wye 277/480V AC, 4-Pole 4-Wire Grounding, L19-20P, Screw Terminal, Black and White

Application

Extra Heavy Duty Industrial

General

Catalog Number	71920NP
Color	Black, White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	20A Triple Gripper Nylon Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	4-Pole
Style	Internal Cord Clamp
Type	Plugs
UPC	781786699021

Dimensions

Dimensions	2.13 in x 2.13 in x 2.86 in
Display Size	Standard Sized
Height	2.86 in
Length	2.13 in
Width	2.13 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current Rating	20 A
Phase	Three Phase
Voltage Rating	3 Phase Y 277/480 VAC
Voltage Rating Description	3 Phase Y 277/480 VAC

Conductor Related

Cord Type	All Listed Portables
Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG

Certifications And Compliance

Nema Rating	L19-20P
-------------	---------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - Bryant Full Line Catalog](#)
[Specifications - 71920NP](#)