



Locking Devices, Industrial, Female Connector Body, 30A 3-Phase Wye 277/480V AC, 4-Pole 5-Wire Grounding, L22-30R, Screw Terminal, Black and White

By Bryant
Catalog # [72230NC](#)



Locking Devices, Industrial, Female Connector Body, 30A 3-Phase Wye 277/480V AC, 4-Pole 5-Wire Grounding, L22-30R, Screw Terminal, Black and White

Application

Heavy Duty Industrial

General

Catalog Number	72230NC
Color	Black, White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	30A Triple Gripper Nylon Connector
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	4-Pole
Style	Internal Cord Clamp
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body
UPC	781786702196

Dimensions

Dimensions	2.13 in x 2.13 in x 3.90 in
Display Size	Standard Sized Product
Height	3.9 in

Length	2.13 in
Width	2.13 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Screw Terminals
Current Rating	30 A
Voltage Rating	3 Phase Y 277/480 VAC
Voltage Rating Description	3 Phase Y 277/480 VAC

Conductor Related

Conductor Range	#12 AWG to #8 AWG
Number Of Wires	5-Wire
Number of Conductors	5-Wire Grounding
Wire Size	#18 AWG to #8 AWG

Certifications And Compliance

Nema Rating	L22-30R
-------------	---------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - Bryant Full Line Catalog](#)
[Specifications - 72230NC](#)