



Locking Devices, Bryant Midget Locking, Industrial, Female Connector Body, 15A 125V, 2-Pole 2-Wire Non-Grounding, ML-1R, Screw Terminal, Black & White



By Bryant
Catalog # 7464N

Locking Devices, Bryant Midget Locking, Industrial, Female Connector Body, 15A 125V, 2-Pole 2-Wire Non-Grounding, ML-1R, Screw Terminal, Black & White

Application

Heavy Duty Industrial

General

Catalog Number	7464N
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	15A Midget Female Connector
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Style	Non-Grounding
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Plugs
UPC	781786638501

Dimensions

Dimensions	1.25 in x 1.25 in x 2.15 in
Display Size	Midget NEMA Locking
Height	2.15 in
Length	1.25 in

Width 1.25 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current Rating	15 A
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Conductor Range	#14 AWG
Number Of Wires	2-Wire
Number of Conductors	2-Pole Non-Grounding
Wire Size	#18 AWG to #12 AWG

Certifications And Compliance

Nema Rating ML-1R

Logistics

Carton Quantity	10
Pallet Quantity	16500

Product Assets

[Catalogs - Bryant Full Line Catalog](#)
[Specifications - 7464N](#)