



# Locking Devices, Bryant Midget Locking, Industrial, Female Connector Body, 15A 125/250V, 3-Pole 3-Wire Non Grounding, ML-3R, Screw Terminal & White

By Bryant  
Catalog # 7484NC



Locking Devices, Bryant Midget Locking, Industrial, Female Connector Body, 15A 125/250V, 3-Pole 3-Wire Non Grounding, ML-3R, Screw Terminal, Black & White

## Application

Heavy Duty Industrial

## General

Catalog Number	7484NC
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	15A Midget Female Connector
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
Style	Non-Grounding
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body
UPC	781786669352

## Dimensions

Dimensions	1.25 in x 1.25 in x 2.15 in
Display Size	Midget NEMA Locking
Height	2.15 in
Length	1.25 in

Width 1.25 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current Rating	15 A
Voltage Rating	125/250 V
Voltage Rating Description	125/250 V

## Conductor Related

Conductor Range	#14 AWG
Number Of Wires	3-Wire
Number of Conductors	3-Wire Non-Grounding
Wire Size	#18 AWG to #12 AWG

## Certifications And Compliance

Nema Rating ML-3R

## Logistics

Carton Quantity	10
Pallet Quantity	5850

## Product Assets

[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - 7484NC](#)