



Straight Blade Devices, Receptacles, Flush Mount Single, Commercial/Industrial Grade, Reinforced Thermoplastic Polyester, 30A 125V, 5-30R

By Bryant
Catalog # 9530FR



Straight Blade Devices, Receptacles, Flush Mount Single,
Commercial/Industrial Grade, Reinforced Thermoplastic
Polyester, 30A 125V, 2-Pole 3-Wire Grounding, 5-30R, Black,
Single Pack

General

Application	Industrial Grade
Catalog Number	9530FR
Color	Black
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Single
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Series	Heavy Duty
Style	Smooth Face
Type	Single Receptacle
UPC	781786676732

Dimensions

Display Size	Standard Sized Product
Weight	0.4 lb

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	3750

Conductor Related

Number Of Wires	3-Wire
Wire Size	#10 AWG to #6 AWG

Certifications And Compliance

Nema Rating	5-30R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	25
-----------------	----

Product Assets

[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY_MX-9530FR-SPEC-EN | REV 6/2024