



Straight Blade Devices, Elastomeric, Female Connector Body, 20A 125V, 2-Pole 3-Wire Grounding, 5-20P, Screw Terminal, Yellow, Water/Dust-Tight Housing



By Bryant
Catalog # [BRY15W33](#)

Straight Blade Devices, Elastomeric, Female Connector Body, 20A 125V, 2-Pole 3-Wire Grounding, 5-20P, Screw Terminal, Yellow, Water/Dust-Tight Housing

Features

- Female Connector Body
- 20A 125V
- 2-Pole 3-Wire Grounding
- 5-20P
- Screw Terminal

General

Catalog Number	BRY15W33
Color	Yellow
Cord Range	0.325"-0.625"
Number Of Poles	2-Pole
Type	Connector Body
UPC	781786378223

Dimensions

Length	4.42 in
Weight	0.3 lb
Width	1.85 in

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3-Wire
-----------------	--------

Certifications And Compliance

Nema Rating	5-20R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	25
-----------------	----

Product Assets

[Catalogs - Bryant Full Line Catalog](#)
[Specifications - BRY15W33](#)