



Locking Devices, Male Plug, 15A 277V AC, 2-Pole 3-Wire Grounding, L7-15P, Screw Terminal, Yellow, Water/Dust-Tight Housing

By Bryant
Catalog # [BRY24W34](#)



Watertight Devices, Locking Devices, Male Plug, 15A 277V AC, 2-Pole 3-Wire Grounding, L7-15P, Screw Terminal, Yellow, Water/Dust-Tight Housing

Performance

- Dielectric voltage:2000V AC if rated 300V or less, 3000V AC if rated above 300V
- Moisture resistance:UL Listed to 3R, 3RX, 4, 4X, 6, 6P, 12
- UV resistance:All exposed materials are UV stabilized
- Flammability:UL94V2 (plugs, connectors, and interiors)

General

Catalog Number	BRY24W34
Color	Yellow
Item Type	15A Watertight Plug
Number Of Poles	2-Pole
Type	Plugs
UPC	781786378261

Dimensions

Dimensions	1.85 in x 1.85 in x 3.21 in
Height	3.21 in
Length	1.85 in
Width	1.85 in

Electrical Ratings

Amperage Rating	15 A
Voltage Rating	277 VAC

Voltage Rating Description 277 VAC

Conductor Related

Number Of Wires 3-Wire
Wire Size #16/3 SJ to #10/3 SJ, #18/3 S to #12/3 S

Certifications And Compliance

Industry Standard(s)

- IP69K
- Listed to UL498
- Certified to CSA C22.2 No. 42
- Meets NEMA® WD-1, WD-6, and ANSI Standards
- IP66 Suitability
- NSF Certified (plugs, connectors and receptacles)

Nema Rating L7-15P

Logistics

Carton Quantity 25

Product Assets

[Catalogs - Bryant Full Line Catalog](#)
[Specifications - BRY24W34](#)