



# Locking Devices, Elastomeric, Female Connector Body, 15A277V AC, 2-Pole 3-Wire Grounding, L7-15R, Screw Terminal, Yellow, Water/Dust-Tight Housing



By Bryant  
Catalog # [BRY25W34](#)

Watertight Devices, Locking Devices, Elastomeric, Female Connector Body, 15A 277V AC, 2-Pole 3-Wire Grounding, L7-15R, Screw Terminal, Yellow, Water/Dust-Tight Housing

## Performance

- Dielectric voltage:2000V AC if rated 300V or less, 3000V AC if rated above 300V
- Moisture resistance:UL Listed to 3R, 3RX, 4, 4X, 6, 6P, 12
- UV resistance:All exposed materials are UV stabilized
- Flammability:UL94V2 (plugs, connectors, and interiors)

## General

Catalog Number	BRY25W34
Color	Yellow
Item Type	15A Watertight Connector
Number Of Poles	2-Pole
Type	Connector Body
UPC	781786378315

## Dimensions

Dimensions	1.85 in x 1.85 in x 4.62 in
Height	4.62 in
Length	1.85 in
Width	1.85 in

## Electrical Ratings

Amperage Rating	15 A
Voltage Rating	277 VAC

Voltage Rating Description 277 VAC

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#16/3 SJ to #10/3 SJ, #18/3 S to #12/3 S

## Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>IP69K</li><li>Listed to UL498</li><li>Certified to CSA C22.2 No. 42</li><li>Meets NEMA® WD-1, WD-6, and ANSI Standards</li><li>IP66 Suitability</li><li>NSF Certified (plugs, connectors and receptacles)</li></ul>
Nema Rating	L7-15R

## Logistics

Carton Quantity 25

## Product Assets

[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - BRY25W34](#)