



Locking Devices, Elastomeric, Female Connector Body, 15A 250V, 2-Pole 3-Wire Grounding, L6-15R, Screw Terminal, Yellow, Water/Dust-Tight Housing



By Bryant
Catalog # BRY25W49

Watertight Devices, Locking Devices, Elastomeric, Female Connector Body, 15A 250V, 2-Pole 3-Wire Grounding, L6-15R, Screw Terminal, Yellow, Water/Dust-Tight Housing

Performance

- Dielectric voltage:2000V AC if rated 300V or less, 3000V AC if rated above 300V
- Moisture resistance:UL Listed to 3R, 3RX, 4, 4X, 6, 6P, 12
- UV resistance:All exposed materials are UV stabilized
- Flammability:UL94V2 (plugs, connectors, and interiors)

General

Catalog Number	BRY25W49
Color	Yellow
Item Type	15A Watertight Connector
Number Of Poles	2-Pole
Type	Connector Body
UPC	781786378339

Dimensions

Dimensions	1.85 in x 1.85 in x 4.62 in
Height	4.62 in
Length	1.85 in
Width	1.85 in

Electrical Ratings

Amperage Rating	15 A
Voltage Rating	250 V

Voltage Rating Description	250 V
----------------------------	-------

Conductor Related

Number Of Wires	3-Wire
Wire Size	#16/3 SJ to #10/3 SJ, #18/3 S to #12/3 S

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">IP69KListed to UL498Certified to CSA C22.2 No. 42Meets NEMA® WD-1, WD-6, and ANSI StandardsIP66 SuitabilityNSF Certified (plugs, connectors and receptacles)
Nema Rating	L6-15R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - Bryant Full Line Catalog](#)
[Specifications - BRY25W49](#)

