



Locking Devices, Elastomeric, Male Plug, 30A 3- Phase Delta 480V AC, 3-Pole 4-Wire Grounding, L16-30P, Screw Terminal, Water/Dust-Tight Housing

By Bryant
Catalog # BRY28W76



Watertight Devices, Locking Devices, Elastomeric, Male Plug, 30A 3-Phase Delta 480V AC, 3-Pole 4-Wire Grounding, L16-30P, Screw Terminal, Yellow, Water/Dust-Tight Housing

Performance

- Dielectric voltage:2000V AC if rated 300V or less, 3000V AC if rated above 300V
- Moisture resistance:UL Listed to 3R, 3RX, 4, 4X, 6, 6P, 12
- UV resistance:All exposed materials are UV stabilized
- Flammability:UL94V2 (plugs, connectors, and interiors)

General

Catalog Number	BRY28W76
Color	Yellow
Item Type	30A Watertight Plug
Number Of Poles	3-Pole
Type	Plugs
UPC	781786378780

Dimensions

Dimensions	2.77 in x 2.77 in x 3.94 in
Height	3.94 in
Length	2.77 in
Width	2.77 in

Electrical Ratings

Amperage Rating	30 A
Voltage Rating	3 Phase 480 VAC
Voltage Rating Description	3 Phase 480 VAC

Conductor Related

Number Of Wires	4-Wire
Wire Size	Min. cords: #12/3 SJ, #16/3 S, #14/4 SJ, #18/4 S, #18/5 S;Max. cord: #8/3 S, #8/4 S, #10/5 S

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> IP69K Listed to UL498 Certified to CSA C22.2 No. 42 Meets NEMA® WD-1, WD-6, and ANSI Standards IP66 Suitability NSF Certified (plugs, connectors and receptacles)
Nema Rating	L16-30P

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - Bryant Full Line Catalog](#)
[Specifications - BRY28W76](#)

