



Straight Blade Devices, Female Connector Body, Heavy Duty, Industrial/Commercial Grade, Straight, 15A 125V, 2-Pole 3-WireGrounding, 5-15R and Black

By Bryant
Catalog # [BRY5269NC](#)



Straight Blade Devices, Female Connector Body, Heavy Duty, Industrial/Commercial Grade, Straight, 15A 125V, 2-Pole 3-WireGrounding, 5-15R, White and Black, Single Pack

Features

- Heavy Duty
- Industrial/Commercial Grade
- Straight
- 15A 125V
- 2-Pole 3- WireGrounding

Application

Extra Heavy Duty Industrial Grade

General

Catalog Number	BRY5269NC
Color	Black and White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	Tech-Spec Triple Gripper
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Series	Industrial
Style	Extra Heavy Duty
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body
UPC	781786005945

Dimensions

Dimensions 2.95 in x 1.52 in x 1.38 in

Display Size	Standard Sized Product
Height	1.38 in
Length	2.95 in
Weight	0.15 lb
Width	1.52 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Conductor Range	#14 AWG to #10 AWG
Number Of Wires	3-Wire
Number of Conductors	3-Wire Grounding

Certifications And Compliance

Nema Rating	5-15R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
Pallet Quantity	4500

Product Assets

[Catalogs - Bryant Full Line Catalog](#)
[Specifications - BRY5269NC](#)

