



Straight Blade Devices, Receptacles, Duplex, Commercial/Industrial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5- 20R, Brown, Single Pack

By Bryant
Catalog # [BRY5362](#)



Straight Blade Devices, Receptacles, Duplex,
Commercial/Industrial Grade, 20A 125V, 2-Pole 3-Wire
Grounding, 5-20R, Brown, Single Pack

Features

- Duplex
- Commercial/Industrial Grade
- 20A 125V
- 2-Pole 3-Wire Grounding
- 5-20R

Application

Extra Heavy Duty Industrial Specification Grade

General

Catalog Number	BRY5362
Color	Brown
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Traditional Duplex
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Series	Extra Heavy Duty
Style	Finder Groove Face
Type	Duplex Receptacle
UPC	781786005204

Dimensions

Dimensions	3.28 in x 1.54 in x 1.16 in
Display Size	Standard Sized Product
Height	1.16 in
Length	3.28 in

Weight	0.25 lb
Width	1.54 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	5-20R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
Pallet Quantity	5500

Product Assets

[Catalogs - Bryant Full Line Catalog](#)
[Specifications - BRY5362](#)