



# Female Connector Body, Heavy Duty, Industrial/Commercial Grade, Straight, 15A 250V, 2-Pole 3- Wire Grounding, 6-15R, White and Black, Single Pack

By Bryant  
Catalog # [BRY5669NC](#)



Straight Blade Devices, Female Connector Body, Heavy Duty, Industrial/Commercial Grade, Straight, 15A 250V, 2-Pole 3- Wire Grounding, 6-15R, White and Black, Single Pack

## Features

- Heavy Duty
- Industrial/Commercial Grade
- Straight
- 15A 250V
- 2-Pole 3- Wire Grounding

## Application

Extra Heavy Duty Industrial Grade

## General

Catalog Number	BRY5669NC
Color	Black and White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	Tech-Spec Triple Gripper
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Series	Industrial
Style	Extra Heavy Duty
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body
UPC	781786005976

## Dimensions

Dimensions	2.95 in x 1.52 in x 1.38 in
Display Size	Standard Sized Product

Height	1.38 in
Length	2.95 in
Weight	0.15 lb
Width	1.52 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250 V

## Conductor Related

Conductor Range	#14 AWG to #10 AWG
Number Of Wires	3-Wire
Number of Conductors	3-Wire Grounding

## Certifications And Compliance

Nema Rating	6-15R
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
Pallet Quantity	4500

## Product Assets

[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - BRY5669NC](#)

