



Straight Blade Devices, Female Connector Body, Valise Series, Industrial/Commercial Grade, Straight, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R



By Bryant
Catalog # [BRY5969Y](#)

Straight Blade Devices, Female Connector Body, Valise Series, Industrial/Commercial Grade, Straight, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Yellow, Single Pack

Features

- Valise Series
- Industrial/Commercial Grade
- Straight
- 15A 125V
- 2-Pole 3-Wire Grounding

Application

Heavy Duty

General

Catalog Number	BRY5969Y
Color	Yellow
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	Valise
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Series	Commercial
Style	Heavy Duty
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body
UPC	781786005860

Dimensions

Dimensions	2.62 in x 1.25 in x 1.12 in
Display Size	Standard Sized Product
Height	1.12 in
Length	2.62 in
Weight	0.3 lb
Width	1.25 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Conductor Range	#14 AWG to #10 AWG
Number Of Wires	3-Wire
Number of Conductors	3-Wire Grounding

Certifications And Compliance

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	10
Pallet Quantity	3600

Product Assets

[Catalogs - Bryant Full Line Catalog](#)
[Specifications - BRY5969Y](#)