



# Straight Blade Devices, Female Connector Body, Valise Series, Industrial/Commercial Grade, Straight, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R



By Bryant  
Catalog # [BRY5969Y](#)

Straight Blade Devices, Female Connector Body, Valise Series, Industrial/Commercial Grade, Straight, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Yellow, Single Pack

## Features

- Valise Series
- Industrial/Commercial Grade
- Straight
- 15A 125V
- 2-Pole 3-Wire Grounding

## Application

Heavy Duty

## General

Catalog Number	BRY5969Y
Color	Yellow
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	Valise
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Series	Commercial
Style	Heavy Duty
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body
UPC	781786005860

## Dimensions

Dimensions	2.62 in x 1.25 in x 1.12 in
Display Size	Standard Sized Product
Height	1.12 in
Length	2.62 in
Weight	0.3 lb
Width	1.25 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Voltage Rating	125 V
Voltage Rating Description	125 V

## Conductor Related

Conductor Range	#14 AWG to #10 AWG
Number Of Wires	3-Wire
Number of Conductors	3-Wire Grounding

## Certifications And Compliance

Nema Rating	5-15R
-------------	-------

## Logistics

Carton Quantity	10
Pallet Quantity	3600

## Product Assets

[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - BRY5969Y](#)

