



Straight Blade Devices, Receptacles, Duplex, Hospital Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Ivory, Single Pack

By Bryant
Catalog # BRY8300I



Straight Blade Devices, Receptacles, Duplex, Hospital Grade,
20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Ivory, Single Pack

Features

- Duplex
- Hospital Grade
- 20A 125V
- 2-Pole 3-Wire Grounding
- 5-20R

Application

Hospital Grade

General

Catalog Number	BRY8300I
Color	Ivory
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Traditional Duplex
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Series	Hospital Grade
Style	Finder Groove Face
Type	Duplex Receptacle
UPC	781786005679

Dimensions

Dimensions	3.28 in x 1.54 in x 1.16 in
Display Size	Standard Sized Product
Height	1.16 in
Length	3.28 in

Weight	0.25 lb
Width	1.54 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	5-20R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
Pallet Quantity	5500

Product Assets

[Catalogs - Bryant Full Line Catalog](#)
[Specifications - BRY8300I](#)