



Straight Blade Devices,
Receptacles, Duplex, Commercial
Grade, 15A 125V, 2-Pole 3-Wire
Grounding, 5-15R, Orange, Single
Pack, Isolated Ground

By Bryant
Catalog # [CR15IG](#)



Straight Blade Devices, Receptacles, Duplex, Commercial Grade,
15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Orange, Single Pack,
Isolated Ground

Features

- Duplex
- Commercial Grade
- 15A 125V
- 2-Pole 3-Wire Grounding
- 5-15R

Application

Commercial Specification Grade

General

Catalog Number	CR15IG
Color	Orange
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Traditional Duplex Smooth Face
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Series	Straight Blade
Style	Smooth Face
Type	Duplex Receptacle
UPC	781786734647

Dimensions

Dimensions	3.28 in x 1.38 in x 0.92 in
Display Size	Standard Sized Product

Height	0.92 in
Length	3.28 in
Weight	0.15 lb
Width	1.38 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - Bryant Full Line Catalog](#)
[Specifications - CR15IG](#)