



# Locking Devices, Industrial, Female Connector Body, 50A 125/250V, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black and White

By Bryant  
Catalog # CS6364



Locking Devices, Industrial, Female Connector Body, 50A 125/250V, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Heavy Duty Black

## Application

Heavy Duty Industrial

## General

Catalog Number	CS6364
Color	Black
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	50A Heavy Duty Connector
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
Style	Extra Heavy Duty
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body
UPC	781786611771

## Dimensions

Dimensions	6.50 in x 2.56 in x 2.56 in
Display Size	Standard Sized Product

Height	2.56 in
Length	6.5 in
Width	2.56 in

## Electrical Ratings

Amperage Rating	50 A
Connectivity	Pressure Terminal Screws
Current Rating	50 A
Voltage Rating	125/250 VAC
Voltage Rating Description	125/250 VAC

## Conductor Related

Conductor Range	#6 AWG
Number Of Wires	4-Wire
Number of Conductors	4-Wire Grounding
Wire Size	#8 AWG to #4 AWG

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - CS6364](#)