



# Locking Devices, Twist-Lock®, Economy, Female Connector Body, 50A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black



By Bryant  
Catalog # [CS8364L](#)

Locking Devices, Economy, Female Connector Body, 50A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black

## Features

- Female Connector Body
- 50A 3-Phase Delta 250V AC
- 3-Pole 4-Wire Grounding
- Non-NEMA
- Screw Terminal

## Application

Heavy Duty Industrial

## General

Catalog Number	CS8364L
Color	Black
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	50A Nylon Connector
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
Style	Heavy Duty
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body
UPC	783585320731

## Dimensions

Dimensions 5.50 in x 2.40 in x 2.40 in

Display Size	Standard
Height	2.4 in
Length	5.5 in
Width	2.4 in

## Electrical Ratings

Amperage Rating	50 A
Connectivity	Screw Terminals
Current Rating	50 A
Voltage Rating	3 Phase 250 VAC
Voltage Rating Description	3 Phase 250 VAC

## Conductor Related

Conductor Range	#6 AWG
Number Of Wires	4-Wire
Number of Conductors	4-Wire Grounding
Wire Size	#18 AWG to #8 AWG

## Certifications And Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

## Logistics

Carton Quantity	30
Pallet Quantity	1620

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - CS8364L](#)

