



# Locking Devices, Twist-Lock®, Economy, Receptacle, 50A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, Non- NEMA, Screw Terminal, Black

By Bryant  
Catalog # CS8369L



Economy, Receptacle, 50A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal

## Features

- 50A 3-Phase Delta 250V AC
- 3-Pole 4-Wire Grounding
- Non-NEMA
- Screw Terminal

## Application

Heavy Duty Industrial

## General

Catalog Number	CS8369L
Color	Black
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	50A Single Armored Heavy Duty Receptacle
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
Style	Heavy Duty
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Receptacle
UPC	783585320755

## Dimensions

Dimensions	3.30 in x 2.10 in x 2.40 in
Display Size	Standard
Height	2.4 in
Length	3.3 in
Width	2.1 in

## Electrical Ratings

Amperage Rating	50 A
Connectivity	Screw Terminals
Current Rating	50 A
Voltage Rating	3 Phase 250 VAC
Voltage Rating Description	3 Phase 250V AC

## Conductor Related

Conductor Range	#6 AWG
Number Of Wires	4-Wire
Number of Conductors	4-Wire Grounding
Wire Size	#14 AWG to #10 AWG

## Logistics

Carton Quantity	30
Pallet Quantity	2340

## Product Assets

[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - CS8369L](#)