



# Industrial Grade, Pendant Controls, Two Button Compact Version, Single Speed Normally Open, Pilot Duty, 240V, Terminal Screws

By Bryant  
Catalog # PCS002



Switches and Lighting Controls, Industrial Grade, Pendant Controls, Two Button Compact Version, Single Speed Normally Open, Pilot Duty, 240V, Terminal Screws, Yellow

## Features

- Pendant Controls
- Two Button Compact Version
- Single Speed Normally Open
- Pilot Duty
- 240V

## General

Actuator	Push Buttons
Catalog Number	PCS002
Color	Yellow
Contact Configuration	Momentary
EU RoHS Indicator	No
Enclosure Type	NEMA 4X
Environmental Conditions	Indoor and Outdoor
Indicator(s) Type	None
Item Type	Complete Unit- 2 Buttons
Material	Non-Metallic
Material - Mounting Hardware	Cable Mounted
Operating Temperature	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Series	Compact

Style	Two Button
Type	Single Speed
UPC	781786406407

## Dimensions

Display Size	Compact
--------------	---------

## Electrical Ratings

Connectivity	Terminal Screws
Contact Rating	Pilot Duty Only
Current Rating	6 A
Phase	Single Phase
Voltage Rating	250V AC Max kV

## Logistics

Carton Quantity	10
Pallet Quantity	550

## Product Assets

[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - PCS002](#)