

1PLD75012HD

by Burndy
Catalog ID: 1PLD75012HD

Prop 65 Notice

UV Rated Black UNITAP



Product Details

General

Hex Key	3/8 in
Installation Torque Recommended in-lb	500 in-lb
Insulation	Y
Number Of Ports	12
Temperature Rating	-40°C to 135°C
Trade Name	UNITAP™
UPC	621945480803

Dimensions

Dimension - L Length Overall mm	416.052
Dimension - Length Overall inch	16.38

Electrical Ratings

Rating - Minimum Voltage	600 V
--------------------------	-------

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)